

**Garant**
**Clamping toolholder DCLNR 95°, for indexable inserts CN., right-hand,  
Shank / insert size: 40/19mm**

**Order data**

Order number	250016 40/19
GTIN	4062406119119
Item class	21T

**Technical description**

Overall length L	250 mm
ISO code toolholder	DCLNR/L 4040S19
Functional width L <sub>4</sub>	50 mm
suitable indexable insert	CN.. 1906..
Clamp, screw, spring	259035 1
Shim	259031 18
Head length L <sub>1</sub>	45 mm
Shim screw	259025 13
Insert size	19 mm
Shank size	40 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 18	259031 18
Shim Type 36	259031 36
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for hexagon, 1/4 inch E 6.3 Hexagon 2 mm	674242 2