



## Burr Z steel – coarse, Carbide, Type: D1009



### Order data

Order number	540740 D1009
GTIN	4045197804846
Item class	52D

### Description

#### Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank  $\varnothing$  6 mm.

#### Application:

Optimised for **use on steel and steel castings**.

### Technical description

Head $\varnothing$	9.6 mm
Shape	D1009
Shape description	ball
Toothing grit designation	coarse
Overall length	54 mm
Shank $\varnothing$	6 mm
Tooth type abbreviation	Z steel
Head length	8 mm
Series	Tooth configuration Z steel
Tool material	Carbide
Type of product	Burr

**User data**

	<b>Suitability</b>	<b>V<sub>c</sub></b>	<b>ISO code</b>
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
GG(G)	suitable		