



Mini burr Z7 – medium, diamond cut, Carbide, Type: C0613



Order data

Order number	546910 C0613
GTIN	4045197724229
Item class	52D

Description

Version:

HOLEX – burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank Ø 3 mm.

Application:

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

Technical description

Overall length	44 mm
Head Ø	6.3 mm
Type of cut	staggered teeth
Toothing grit designation	medium
Shape description	Ball nose
Shape	C0613
Tooth type abbreviation	Z7
Shank Ø	3 mm
Head length	12.7 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

User data

	Suitability	V_c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		