



Burr Z steel – coarse, Carbide, Type: D1210



Order data

| | |
|--------------|---------------|
| Order number | 540740 D1210 |
| GTIN | 4045197804853 |
| Item class | 52D |

Description

Version:

The innovative tooth geometry permits **very high metal removal rates** combined with **smooth cutting and good guidance accuracy**. The optimised chip formation (no pointed chips) ensures good surface quality. Shank \varnothing 6 mm.

Application:

Optimised for **use on steel and steel castings**.

Technical description

| | |
|---------------------------|-----------------------------|
| Shank \varnothing | 6 mm |
| Head \varnothing | 12.7 mm |
| Shape | D1210 |
| Overall length | 56 mm |
| Tooth type abbreviation | Z steel |
| Toothing grit designation | coarse |
| Shape description | ball |
| Head length | 11 mm |
| Series | Tooth configuration Z steel |
| Tool material | Carbide |
| Type of product | Burr |

User data

| | Suitability | V_c | ISO code |
|--------------------------------|--------------------|----------------------|-----------------|
| Steel < 900 N/mm ² | suitable | | |
| Steel < 1400 N/mm ² | suitable | | |
| Steel < 55 HRC | suitable | | |
| Steel < 60 HRC | suitable | | |
| Steel < 67 HRC | suitable | | |
| GG(G) | suitable | | |