

**Mini burr Z7 – medium, diamond cut, Carbide, Type: E0610****Order data**

Order number	546910 E0610
GTIN	4045197724274
Item class	52D

**Description****Version:**

**HOLEX** – burrs are manufactured from highest quality carbide with high wear-resistance and maximum cutting edge strength, using only the latest CNC machines. Steel shanks are used when the head diameter is larger than the shank diameter, otherwise they are made from solid carbide.

Carbide mini burr with shank  $\varnothing$  3 mm.

**Application:**

Suitable for use with power tools and industrial robots, on almost all materials. For deburring, edge breaking, cleaning, weld and surface preparation.

**Technical description**

Tooth type abbreviation	Z7
Shape	E0610
Shape description	Teardrop
Type of cut	staggered teeth
Head $\varnothing$	6.3 mm
Toothing grit designation	medium
Overall length	42 mm
Shank $\varnothing$	3 mm
Head length	9.5 mm
Series	#Tooth configuration Z7

Tool material	Carbide
Type of product	Burr

**User data**

	Suitability	V <sub>c</sub>	ISO code
Steel < 900 N/mm <sup>2</sup>	suitable		
Steel < 1400 N/mm <sup>2</sup>	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
INOX	suitable only under restricted conditions		
Ti	suitable only under restricted conditions		
GG(G)	suitable		
Uni	suitable		