


Garant
Flap wheel (CER), 120 grit, Head Ø×head width: 20X20 mm

Order data

Order number	554170 20X20
GTIN	4062406123918
Item class	51E

Description
Version:

Flap strips bonded on to the shank of the tool.
Abrasive strips covered with **ceramic grit (CER)**.

Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: Ceramic

Shank Ø: 6 mm

recommended speed: 20000 rpm

maximum speed: 38200 rpm

Technical description

Shank Ø	6 mm
recommended speed	20000 rpm
Head width	20 mm
Head Ø	20 mm
Grit	120

maximum speed	38200 rpm
Grinding media	Ceramic grit (CER)
Grinding medium code	Ceramic
Product name attribute	120 grit
Type of product	Flap wheel