

Garant

GARANT Master Alu PickPocket solid carbide roughing end mill HPC, DLC, Ø e8 DC: 6mm



Order data

Order number	202004 6
GTIN	4062406125929
Item class	11X

Description

Version:

With the latest generation of DLC coating sp².

For roughing and finishing.

Up to 2 × D into solid material at very high feed rates and smooth cutting action.

Very high feed rates when plunging vertically.

Ramping capability up to 45°.

Advantage:

Optimised flute form, eccentric relief ground, generous chip spaces.

Tolerance nominal Ø: e8

No. of teeth Z: 3

Helix angle: 42°

Direction of infeed: horizontal, oblique and vertical

Shank: DIN 6535 HA to h6

Balance quality with shank: G 2.5 with HA

No. of teeth Z: 3

Flute length L_c: 13 mm

Overhang length L₁ incl. recess: 19 mm

Recess Ø D₁: 5.8 mm

Overall length L: 57 mm

Shank Ø D_s: 6 mm

Technical description

Flute length L _c	13 mm
-----------------------------	-------

Shank	DIN 6535 HA to h6
Balance quality with shank	G 2.5 with HA
Direction of infeed	horizontal, oblique and vertical
Tolerance nominal \varnothing	e8
Feed f_z for side milling in short-chipping aluminium	0.08 mm
Shank $\varnothing D_s$	6 mm
Feed f_z for slot milling in short-chipping aluminium	0.06 mm
Helix angle	42°
Recess $\varnothing D_1$	5.8 mm
No. of teeth Z	3
Overall length L	57 mm
Cutting edge $\varnothing D_c$	6 mm
Overhang length L_1 incl. recess	19 mm
Corner rounding r_v	0.2 mm
Series	Master Alu
Coating	DLC
Tool material	Solid carbide
Standard	DIN 6527
Type	W
Helix angle characteristic	unequal spacing
Spacing of the cutters	unequal spacing
Cutting width a_e for milling operation	Full slot cutting depth 1xD
Cutting width a_e for milling operation	Full slot cutting depth 1xD
Through-coolant	no
Machining strategy	HPC
Colour ring	yellow
Type of product	End / face mill

User data

	Suitability	V_c	ISO code
Aluminium	Suitable	550 m/min	N
Aluminium (short chipping)	suitable	500 m/min	N
Alu > 10% Si	suitable	450 m/min	N
PMMA acrylic	Suitable	200 m/min	N
PE-HD	Suitable	160 m/min	N
PA 66	Suitable	200 m/min	N
PEEK	Suitable	150 m/min	N
PF 31	Suitable	130 m/min	N
PVDF GF20	Suitable	180 m/min	N
POM GF25	Suitable	160 m/min	N
PA 66 GF30	Suitable	150 m/min	N
PEEK GF30	Suitable	130 m/min	N
PTFE CF25	Suitable	160 m/min	N
Honeycomb sandwich	suitable only under restricted conditions	300 m/min	N
Cu	Suitable	160 m/min	N
CuZn	Suitable	200 m/min	N
wet maximum	suitable		
wet minimum	suitable only under restricted conditions		
dry	suitable only under restricted conditions		
Air	suitable		

Services

Shank grinding Type HB

129100 HB