



Abrasive flap disc speed ZA, flat, Ø 125 mm, Grit: 80



Order data

Order number	565295 80
GTIN	4062406159634
Item class	52M

Description

Version:

- **High-quality zirconium aluminium oxide (ZA) for high abrasive performance.**
- **Glass fibre pad for optimum contact pressure.**
- **Suitable for both steel and stainless steel.**
- **Best results on angle grinders of all power classes.**

speed - flat flap strip arrangement, for **high metal removal rate** and long tool life.

Application:

Precise chamfering, edge smoothing and surface abrasion.

maximum circumferential speed: 80 m/s

Shape description: flat

Bore Ø: 22.23 mm

Technical description

Bore Ø	22.23 mm
Shape description	flat
Grinding media	Zirconium abrasive (ZA)

Grinding medium code	ZA
Iron, sulphur and chlorine constituents	< 0.1 %
Product name attribute	Ø 125 mm
optimised for material	INOX
optimised for material	Steel
maximum circumferential speed	80 m/s
Type of product	Abrasive flap disc

User data

	Suitability	V _c	ISO code
Steel < 900 N/mm ²	suitable		
Steel < 1400 N/mm ²	suitable		
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
INOX	suitable		
Ti	suitable only under restricted conditions		
GG(G)	suitable only under restricted conditions		
Uni	suitable		
dry	suitable		