

Garant

Clamping toolholder STGCL 90°, for indexable inserts TC., left-hand, Shank / insert size: 12/11mm



Order data

Order number	260907 12/11
GTIN	4045197805911
Item class	21T

Technical description

Functional width L_4	16 mm
suitable indexable insert	TC.. 1102..
Shank size	12 mm
Head length L_1	19 mm
Overall length L	80 mm
Insert size	11 mm
ISO code toolholder	STGCR/L 1212F11
Pack of insert screws	269028 18
Standard	DIN ISO 5610
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Set of insert screws Type 18	269028 18
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15