


**Side lock arbor Form AD, BT 40 A = 100, Clamping range  $\varnothing$  D1: 6mm**

**Order data**

|              |               |
|--------------|---------------|
| Order number | 302617 6      |
| GTIN         | 4062406230326 |
| Item class   | 32A           |

**Description**
**Version:**

All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.

**Application:**

For clamping tools with side flats to DIN 1835 B and DIN 6535 HB.

**Optional extras:**

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

**Technical description**

|                                       |                     |
|---------------------------------------|---------------------|
| Spare clamping screw No. 30 9900      | 6                   |
| Overhang dimension A                  | 100 mm              |
| External $\varnothing$ D              | 25 mm               |
| Clamping $\varnothing$ D <sub>1</sub> | 6 mm                |
| Adapter                               | BT 40 A = 100       |
| Standard                              | DIN 6359            |
| Arbor standard                        | JIS B6339           |
| Arbor standard                        | ISO 7388-2          |
| Shape                                 | AD                  |
| Balance quality G at rotational speed | G 6.3 at 18,000 rpm |

|                    |                 |
|--------------------|-----------------|
| Concentricity      | ≤ 3 μm          |
| Machining strategy | HPC             |
| Type of product    | Side lock arbor |

---

## Accessories

|   |          |
|---|----------|
| Spare clamping screw for chucks with clamping Ø D1 6 mm | 309900 6 |
|---|----------|