



Manual vice for drilling machines, Jaw width A: 100mm



Order data

Order number	365055 100
GTIN	4062406188634
Item class	32D

Description

Version:

- Can be used horizontally, vertically or laterally.
- Sturdy and handy design.
- Jaws through hardened and ground.
- Uniform total length. (spindle retracts into handle!)
- Universal fastening capability due to long holes.
- Movable jaw with guides at the sides.
- Fixed jaw with three vertical prismatic and one horizontal prismatic section.
- With detachable crank.

Application:

For clamping components on drilling machines.

Material:

Cast iron body.

Accuracy:

Within 0.20 mm.

Technical description

Base body length a	191 mm
Overall height c	64 mm
Jaw height C	30 mm

Clamping range b	101 mm
Weight	4.8 kg
Type of product	Drilling machine vice

Accessories

Pair of spare jaws (2 pieces) for manual vice for drilling machines for type 100	365046 100
--	------------