

Garant**Solid carbide jobber drill, TiAlN, Ø DC h7: 2,3mm****Order data**

Order number	122251 2,3
GTIN	4045197749024
Item class	11E

Description**Version:****Similar to DIN 338.**

Nominal Ø and shank Ø equal.

TiAlN coating for even better performance.

Note:

Flute length $L_c = L_2 + 1.5 \times D_c$.

Non slip clamping in drill chuck No. 341050 with diamond coated jaws.

Through-coolant: no

Standard: DIN 338

Tolerance nominal Ø: h7

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 23.6 mm

Tolerance nominal Ø: h7

Overall length L: 53 mm

Shank Ø D_s : 2.3 mm

Feed f in steel < 1100 N/mm²: 0.05 mm/rev.

Technical description

Overall length L	53 mm
Tolerance nominal Ø	h7
Standard	DIN 338
Number of cutting edges Z	2
Flute length L_c	27 mm
Shank tolerance	h7

Nominal $\varnothing D_c$	2.3 mm
Shank $\varnothing D_s$	2.3 mm
Feed f in steel $< 1100 \text{ N/mm}^2$	0.05 mm/rev.
recommended maximum drilling depth L_2	23.6 mm
Coating	TiAlN
Tool material	solid carbide
Type	N
Point angle	118 °
Helix angle	30 °
Shank	Parallel shank to h7
Through-coolant	no
Colour ring	without
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Alu plastics	suitable only under restricted conditions	260 m/min	N
Aluminium (short chipping)	suitable	180 m/min	N
Alu $> 10\% \text{ Si}$	suitable	180 m/min	N
Steel $< 500 \text{ N/mm}^2$	suitable	90 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	90 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	80 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	60 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	35 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	35 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	25 m/min	M
Ti $> 850 \text{ N/mm}^2$	suitable	25 m/min	S

GG(G)	suitable	90 m/min	K
CuZn	suitable	180 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		
dry	suitable only under restricted conditions		