

**HOLEX****Locking C clamp with movable jaws, overall length: 455mm****Order data**

Order number	709401 455
GTIN	4062406241063
Item class	72B

**Description****Version:**

Deep long-reach clamp for exceptionally wide components. Body with adjustable screw, clamp, and release lever. Nickel-plated handles and frame.

With movable jaws to protect the component.

**Application:**

Particularly suitable for clamping profiled shapes when drilling, welding or screw-fixing; large reach.

**Spare part:**

Spare spring No. 708301 size 10.

**Technical description**

overall length	455 mm
Throat	250 mm
Jaw capacity	220 mm
Clamping jaws	movable
Surface	nickel-plated
Type of product	Grip wrench

**Accessories**

Spring Type 10

708301 10