

Garant**Face mill arbor with cooling channel bore, HSK-A 63 medium, Spigot Ø d1: 40mm****Order data**

Order number	306541 40
GTIN	4045197763570
Item class	31A

Description**Version:**

- Clamping Ø 40 with 4 tapped holes for drive blocks to DIN 2079.
- With RFID/Balluffchip bore.
- Increased collar contact surface.
- HSK mating faces machined.

With **cooling channel bore**.

Application:

For clamping shell end mills and milling cutter heads.

Supplied with:

Lock screw

Optional extras:

Coolant tube No. 309880, socket wrench No. 309890, toggle spanner No. 309840, milling cutter lock screw for internal coolant supply No. 309861.

Technical description

Spigot Ø d ₁	40 mm
Overhang dimension A	80 mm
Suitable toggle spanner No. 309840	40
Milling mandrel length L ₄	27 mm

External Ø D	89 mm
Spare milling cutter lock screw No. 309860 / 309861	40
Clamping Ø D ₁	40 mm
Adapter	HSK-A 63 medium
Arbor standard	DIN 69893
Arbor standard	DIN 69882-3
Arbor standard	ISO 12164-1
Shape	A
Cooling channel bore	cannot be plugged
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 6 µm
Machining strategy	HPC
Type of product	Milling head arbor

Accessories

Toggle spanner for mandrel Ø 40 mm	309840 40
Milling cutter lock screw for mandrel Ø 40 mm	309860 40