

**Indexable insert for turning TCMT 16T308, for medium machining, Grade: HBT130****Order data**

Order number	261019 HBT130
GTIN	4062406257545
Item class	22D

Technical description

Cutting depth a_p	0.3 - 2.5 mm
Coating	TiCN
Corner radius	0.8 mm
Grade	HBT130
Cutting speed v_c main application	50 - 200 m/min
Feed f	0.05 - 0.35 mm/rev.
Number of changes/inserts	3
Tool material	Carbide
Chip breaker	MM
Cutting conditions	slightly interrupted
ISO code indexable insert	TCMT 16T308

Main application	M
Finishing/roughing assignment	Skrubbearbejdning-sletbearbejdning
Type of product	Indexable insert for turning