

Garant

**Clamping toolholder DCLNR 95°, for indexable inserts CN., right-hand,
Shank / insert size: 32/16mm**



Order data

Order number	250016 32/16
GTIN	4045197771957
Item class	21T

Technical description

Head length L ₁	40 mm
Overall length L	170 mm
ISO code toolholder	DCLNR/L 3232P16
Insert size	16 mm
Shim screw	259025 11
suitable indexable insert	CN.. 1606..
Shim	259031 35
Functional width L ₄	40 mm
Clamp, screw, spring	259035 6
Shank size	32 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	95 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Type of product	Boring bar

Accessories

Shim screw Type 11	259025 11
Shim Type 35	259031 35
8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm	659874 50
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659906 1600
Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm	659957 1600
Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX25	674248 TX25