

Garant
Clamping toolholder DCLNL 95°, for indexable inserts CN., left-hand, Shank / insert size: 25/16mm

Order data

| | |
|--------------|---------------|
| Order number | 250017 25/16 |
| GTIN | 4045197771971 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| Insert size | 16 mm |
| Shim | 259031 35 |
| ISO code toolholder | DCLNR/L 2525M16 |
| Functional width L ₄ | 32 mm |
| Overall length L | 150 mm |
| suitable indexable insert | CN.. 1606.. |
| Shim screw | 259025 11 |
| Head length L ₁ | 36 mm |
| Shank size | 25 mm |
| Clamp, screw, spring | 259035 6 |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 95 degrees |
| Application | External longitudinal turning |

| | |
|-----------------|-------------------------------|
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|---|-------------|
| Shim screw Type 11 | 259025 11 |
| Shim Type 35 | 259031 35 |
| 8 mm blade with magnet with 1/4 inch bit holder overall length 50 mm | 659874 50 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm | 659906 1600 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 1600 cNm | 659957 1600 |
| Precision Bit for Torx®, 1/4 inch E 6.3 Torx® profile TX25 | 674248 TX25 |