

**Garant**

**Clamping toolholder SCRCR 75°, for indexable inserts CC., right-hand,  
Shank / insert size: 16/09mm**



## Order data

Order number	260004 16/09
GTIN	4045197772503
Item class	21T

## Technical description

ISO code toolholder	SCRCR/L 1616H09
Functional width L <sub>4</sub>	17 mm
Head length L <sub>1</sub>	15 mm
Pack of insert screws	269028 2
Shim screw	269013 2
Shim	269005 1
suitable indexable insert	CC.. 09T3..
Insert size	9 mm
Overall length L	100 mm
Shank size	16 mm
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning

Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Shim Type 1	269005 1
Shim screw Type 2	269013 2
Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15