

**Garant**
**Clamping toolholder SCRCL 75°, for indexable inserts CC., left-hand, Shank / insert size: 8/06mm**

**Order data**

Order number	260005 8/06
GTIN	4045197772558
Item class	21T

**Technical description**

suitable indexable insert	CC.. 0602..
Functional width L <sub>4</sub>	9 mm
Insert size	6 mm
Shank size	8 mm
Head length L <sub>1</sub>	10 mm
ISO code toolholder	SCRCR/L 0808D06
Pack of insert screws	269028 22
Overall length L	60 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	75 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product	Boring bar
-----------------	------------

---

## Accessories

Set of insert screws Type 22	269028 22
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX8	674248 TX8