

Garant

**Clamping toolholder SCACR 90°, for indexable inserts CC., right-hand,
Shank / insert size: 16/09mm**



Order data

Order number	260014 16/09
GTIN	4045197797575
Item class	21T

Technical description

Head length L ₁	16 mm
Shank size	16 mm
suitable indexable insert	CC.. 09T3..
Pack of insert screws	269021 2
Overall length L	150 mm
Functional width L ₄	16 mm
Insert size	9 mm
ISO code toolholder	SCACR/L 1616M09
Standard	Works standard
Application type	right-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15