

Garant

Clamping toolholder SCACL 90°, for indexable inserts CC., left-hand, Shank / insert size: 16/09mm



Order data

| | |
|--------------|---------------|
| Order number | 260015 16/09 |
| GTIN | 4045197797834 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| ISO code toolholder | SCACR/L 1616M09 |
| Functional width L ₄ | 16 mm |
| Insert size | 9 mm |
| Shank size | 16 mm |
| suitable indexable insert | CC.. 09T3.. |
| Pack of insert screws | 269021 2 |
| Overall length L | 150 mm |
| Head length L ₁ | 16 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 90 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--------------------------------------------------------------------------------------|-------------|
| Insert screw Type 2 | 269021 2 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15 | 674248 TX15 |