

Garant**ER compensating floating holder Cylindrical, Type: 25-25****Order data**

Order number	319780 25-25
GTIN	4062406276706
Item class	31V

Description**Version:**

Compensating holder with ER collet adaption. **Adjustable radial and angular compensation.** With through coolant feed.

Application:

Optimum for compensating alignment errors between workpiece and tool, for instance when reaming or tapping (without tension / compression compensation). For use primarily on lathes, but also suitable for milling machines.

Technical description

Shank \varnothing d	25 mm
for ER collets	25
External \varnothing D	57 mm
Overhang dimension A	53 mm
Radial compensation	1 mm
suitable for ER size	25
Through-coolant	yes
Type of product	Collet chuck

