

Garant
Clamping toolholder SDACL 90°, for indexable inserts DC., left-hand, Shank / insert size: 8/07mm

Order data

| | |
|--------------|---------------|
| Order number | 260299 8/07 |
| GTIN | 4045197797902 |
| Item class | 21T |

Technical description

| | |
|---------------------------------|-------------------------------|
| Pack of insert screws | 269021 1 |
| suitable indexable insert | DC.. 0702.. |
| ISO code toolholder | SDACR/L 0808M07 |
| Overall length L | 150 mm |
| Head length L ₁ | 12.7 mm |
| Functional width L ₄ | 8 mm |
| Insert size | 7 mm |
| Shank size | 8 mm |
| Standard | Works standard |
| Application type | left-hand |
| Through-coolant | no |
| Setting angle κ | 90 degrees |
| Application | External longitudinal turning |
| Application | External longitudinal turning |
| Type of product | Boring bar |

Accessories

| | |
|--|------------|
| Insert screw Type 1 | 269021 1 |
| Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm | 659957 500 |
| PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7 | 674248 TX7 |