

Garant**Clamping toolholder SDACL 90°, for indexable inserts DC., left-hand, Shank / insert size: 10/07mm****Order data**

Order number	260299 10/07
GTIN	4045197797919
Item class	21T

Technical description

Insert size	7 mm
Pack of insert screws	269021 1
Functional width L ₄	10 mm
suitable indexable insert	DC.. 0702..
ISO code toolholder	SDACR/L 1010M07
Shank size	10 mm
Overall length L	150 mm
Head length L ₁	15 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7