

**Garant**

**Carbide boring bar E.. SVLCL 95°, for indexable inserts VC., left-hand, Shank Ø / insert size: 12/07mm**


**Order data**

Order number	261333 12/07
GTIN	4062406283605
Item class	21T

**Technical description**

ISO code toolholder	E12K SVLCR/L07
Pack of insert screws	269028 26
Minimum pre-drill Ø $D_{min}$	15.5 mm
Head length $L_1$	40 mm
Neck width $L_4$	9 mm
Centre offset $L_3$	9 mm
Overall length $L$	125 mm
Clamping height $L_2$	11 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Setting angle $\kappa$	95 degrees
Usable depth $T$	6 mm
Shank Ø $D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------