

Garant
Clamping toolholder SDACL 90°, for indexable inserts DC., left-hand, Shank / insert size: 12/11mm

Order data

Order number	260299 12/11
GTIN	4045197797940
Item class	21T

Technical description

Pack of insert screws	269021 2
Overall length L	150 mm
suitable indexable insert	DC.. 11T3..
Shank size	12 mm
Insert size	11 mm
ISO code toolholder	SDACR/L 1212M11
Functional width L ₄	12 mm
Head length L ₁	18 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15