

**Garant**
**Clamping toolholder SDACL 90°, for indexable inserts DC., left-hand, Shank / insert size: 16/11mm**

**Order data**

Order number	260299 16/11
GTIN	4045197797957
Item class	21T

**Technical description**

Overall length L	150 mm
suitable indexable insert	DC.. 11T3..
ISO code toolholder	SDACR/L 1616M11
Shank size	16 mm
Pack of insert screws	269021 2
Insert size	11 mm
Functional width L <sub>4</sub>	16 mm
Head length L <sub>1</sub>	20 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

## Accessories

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15