

**Garant**

**Clamping toolholder SDNCN 62,5°, for indexable inserts DC., neutral, Shank / insert size: 16/11mm**



## Order data

Order number	260301 16/11
GTIN	4045197797988
Item class	21T

## Technical description

ISO code toolholder	SDNCN 1616M11
Overhang L <sub>1</sub> neutral holders	21 mm
Pack of insert screws	269021 2
suitable indexable insert	DC.. 11T3..
Insert size	11 mm
Overall length L neutral holders	150 mm
Functional width L <sub>4</sub> neutral holders	8.6 mm
Shank size	16 mm
Standard	Works standard
Application type	neutral
Through-coolant	no
Setting angle κ	62.5 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

---

**Accessories**

Insert screw Type 2	269021 2
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX15	674248 TX15