

Garant

Carbide boring bar E.. SVLCL 95°, for indexable inserts VC.., left-hand, Shank Ø / insert size: 16/07mm


Order data

Order number	261333 16/07
GTIN	4062406285517
Item class	21T

Technical description

Overall length L	150 mm
Insert size	7 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 26
Setting angle κ	95 degrees
Clamping height L_2	15 mm
ISO code toolholder	E16M SVLCR/L07
Centre offset L_3	11 mm
Minimum pre-drill $\varnothing D_{\min}$	19.5 mm
Head length L_1	55 mm
Neck width L_4	14.5 mm
Usable depth T	5 mm
Shank $\varnothing D_s$	16 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------