

Garant

**Carbide boring bar E.. SVVCR 72,5°, for indexable inserts VC., right-hand,
Shank Ø / insert size: 8/05mm**


Order data

Order number	261336 8/05
GTIN	4062406285524
Item class	21T

Technical description

Overall length L	80 mm
Minimum pre-drill Ø D _{min}	10.2 mm
Insert size	5 mm
ISO code toolholder	E08F SVVCR/L05
Clamping height L ₂	7.5 mm
Neck width L ₄	6 mm
suitable indexable insert	VC.. 0501..
Pack of insert screws	269028 27
Centre offset L ₃	5.5 mm
Setting angle κ	72.5 degrees
Head length L ₁	26 mm
Usable depth T	3,5 mm
Shank Ø D _s	8 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8×D

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 26	269028 26
------------------------------	-----------