

Garant
Clamping toolholder STJCL 93°, for indexable inserts TC., left-hand, Shank / insert size: 10/11mm

Order data

Order number	260905 10/11
GTIN	4045197798039
Item class	21T

Technical description

Overall length L	150 mm
Shank size	10 mm
Pack of insert screws	269021 1
Functional width L ₄	10 mm
Insert size	11 mm
ISO code toolholder	STJCR/L 1010M11
Head length L ₁	16 mm
suitable indexable insert	TC.. 1102..
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	93 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Insert screw Type 1	269021 1
Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm	659957 500
PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7	674248 TX7