

Garant

Clamping toolholder SVACL 90°, for indexable inserts VC., left-hand, Shank / insert size: 10/11mm



Order data

Order number	261315 10/11
GTIN	4045197798138
Item class	21T

Technical description

Head length L ₁	26 mm
Overall length L	150 mm
suitable indexable insert	VC.. 1103..
Shank size	10 mm
Functional width L ₄	10 mm
ISO code toolholder	SVACR/L 1010M11
Pack of insert screws	269021 1
Insert size	11 mm
Standard	Works standard
Application type	left-hand
Through-coolant	no
Setting angle κ	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Type of product	Boring bar

Accessories

Torque screwdriver with scale, to take interchangeable blades maximum torque 200 cNm

659957 200

PrecisionBit for Torx®, 1/4 inch E 6.3 Torx® profile TX7

674248 TX7