




## Flap wheel (A), 40 grit, Head Ø×head width: 40X15 mm



### Order data

Order number	554095 40X15
GTIN	4045197803221
Item class	52E

### Description

#### Version:

Flap strips bonded on to the shank of the tool.

Abrasive strips covered with **regular Aluminium Oxide (A)**.

#### Application:

Primarily for finish grinding and polishing tasks on larger radii in tool and mould making, for vessel and machine fabrication. The abrasive strips adapt to the contours of the component.

Grinding medium code: A

Shank Ø: 6 mm

recommended speed: 12000 rpm

maximum speed: 19100 rpm

### Technical description

Head width	15 mm
Head Ø	40 mm
recommended speed	12000 rpm
maximum speed	19100 rpm

Shank Ø	6 mm
Grit	40
Grinding media	Aluminium Oxide grit (A)
Grinding medium code	A
Product name attribute	40 grit
Type of product	Flap wheel