

Garant

Carbide boring bar E.. SVXCL 113°, for indexable inserts VC., left-hand, Shank Ø / insert size: 12/07mm


Order data

Order number	261369 12/07
GTIN	4062406285821
Item class	21T

Technical description

suitable indexable insert	VC.. 0702..
ISO code toolholder	E12K SVXCR/L07
Setting angle κ	113 degrees
Head length L_1	40 mm
Centre offset L_3	9 mm
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
Pack of insert screws	269028 26
Clamping height L_2	11 mm
Overall length L	125 mm
Overhang L_1	96 mm
Usable depth T	3 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	left-hand
Boring depth up to	8xD

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------