

**Garant**

**Carbide boring bar E.. SVXCR 113°, for indexable inserts VC., right-hand,  
Shank Ø / insert size: 12/07mm**


**Order data**

Order number	261368 12/07
GTIN	4062406285784
Item class	21T

**Technical description**

Setting angle $\kappa$	113 degrees
Head length $L_1$	40 mm
Overall length $L$	125 mm
Centre offset $L_3$	9 mm
Clamping height $L_2$	11 mm
ISO code toolholder	E12K SVXCR/L07
Insert size	7 mm
Minimum pre-drill $\varnothing D_{\min}$	15.5 mm
suitable indexable insert	VC.. 0702..
Pack of insert screws	269028 26
Overhang $L_1$	96 mm
Usable depth $T$	3 mm
Shank $\varnothing D_s$	12 mm
Standard	Works standard
Application type	right-hand
Boring depth up to	8xD

Tool material	Carbide
Through-coolant	yes
Application	Internal longitudinal turning
Type of product	Boring Bar

---

## Accessories

Set of insert screws Type 27	269028 27
------------------------------	-----------