



Rubber backing pad shank Ø 6 mm hard, External Ø mm / Hardness: 75mm



Order data

| | |
|--------------|---------------|
| Order number | 553927 75 |
| GTIN | 4062406301149 |
| Item class | 52E |

Description

Version:

Optimum connection between the backing pad and grinding disc by the quick-clamping system (internal thread). Easy and quick disc replacement by hand, even after heavy use.

Rubber backing pad **shank Ø 6 mm**. To take grinding discs with the **metal lock quick-clamping system**.

Application:

For efficient sanding down of small areas, even with varying contours in tool, mould and model making, machine, plant and container building.

Degree of hardness: hard

maximum speed: 20000 min⁻¹

Technical description

| | |
|--------------------|-------------------------|
| Degree of hardness | hard |
| External Ø | 75 mm |
| maximum speed | 20000 min ⁻¹ |
| Type of product | Backing pad |

