

Garant**GARANT Master Tap machine tap HSS-E-PM, ALTiX, UNC: 1-8****Order data**

Order number	133360 1-8
GTIN	4062406208028
Item class	111

Description**Version:**

GARANT Master Tap universal taps, designed for use in a wide spectrum of materials with high process reliability.

- **HSS-E-PM tool material for maximum wear resistance.**
- **Reduced coefficient of friction due to the new high-performance coating.**
- **Special geometry for optimum swarf evacuation.**

Application:

For UNC uniform coarse threads ASME – B1.1.

Thread type: UNC

Tool material: HSS E PM

Standard: DIN 376

Threads per inch: 8

Thread Ø: 25.4 mm

Overall length L: 160 mm

Shank Ø D_s: 18 mm

Shank square □: 14.5 mm

Tapping hole Ø: 22.25 mm

Technical description

Shank square □	14.5 mm
Tool material	HSS E PM
Number of clamping slots	4
Tapping hole Ø	22.25 mm
Thread pitch	3.175 mm

Shank $\varnothing D_s$	18 mm
Thread depth	76.2 mm
Thread type	UNC
Thread \varnothing	25.4 mm
Standard	DIN 376
Threads per inch	8
Thread size	1-8 UNC
Number of cutting edges Z	4
Overall length L	160 mm
Series	Master Tap
Coating	AlTiX
Flank angle	60°
Tolerance class	2BX
Taper lead form	B
Shank	Plain shank with h9
Through-coolant	no
Application for type of drilling	up to 3×D for through holes
Cutting direction	right-hand
Type of threading tool	Machine tap for dynamic machining
Colour ring	green
Type of product	Tap

User data

	Suitability	V_c	ISO code
Alu plastics	suitable	30 m/min	N
Aluminium (short chipping)	suitable	35 m/min	N
Alu > 10% Si	suitable	20 m/min	N
Steel < 500 N/mm ²	suitable	30 m/min	P

Steel < 750 N/mm ²	suitable	30 m/min	P
Steel < 900 N/mm ²	suitable	25 m/min	P
Steel < 1100 N/mm ²	suitable	12 m/min	P
Steel < 1400 N/mm ²	suitable	8 m/min	P
INOX < 900 N/mm ²	suitable	10 m/min	M
INOX > 900 N/mm ²	suitable	8 m/min	M
GG(G)	suitable	20 m/min	K
CuZn	suitable	20 m/min	N
Uni	suitable		
Oil	suitable		
wet maximum	suitable		