

Garant
Solid carbide HPC drill plain shank DIN 6535 HA, TiAlN, Ø DC m6 (mm or inch): 15

Order data

Order number	123008 15
GTIN	4045197569998
Item class	11E

Description
Version:

Cutting chisel edge with **high centring accuracy** due to **strong core and special point geometry**. High roundness and alignment accuracy of the deep hole, thanks to **4 guide chamfers**. Outstanding chip evacuation due to **4 internal cooling channels** from Ø 3.8 mm. Up to 3.7 mm Ø with 2 internal cooling channels. **Straight major cutting edges** with honed edges and special flute profile for **short chips**, even on long chipping materials.

Note:

Form HB and HE supplied at the same price as HA.

Form **HB**: order with **No. 123010**.

Form **HE**: order with **No. 123008 + 129100HE**.

Flute length $L_c = L_2 + 1.5 \times D_c$.

Standard: Manufacturer's standard

Tolerance nominal Ø: m6

Number of cutting edges Z: 2

recommended maximum drilling depth L_2 : 129.5 mm

Tolerance nominal Ø: m6

Overall length L: 203 mm

Shank Ø D_s : 16 mm

Feed f in stainless steel > 900 N/mm²: 0.2 mm/rev.

Technical description

Shank tolerance	h6
Number of cutting edges Z	2
Nominal Ø D_c	15 mm

Flute length L_c	152 mm
Feed f in stainless steel $> 900 \text{ N/mm}^2$	0.2 mm/rev.
Tolerance nominal $\varnothing$	m6
Shank $\varnothing D_s$	16 mm
Overall length L	203 mm
Standard	Manufacturer's standard
recommended maximum drilling depth L_2	129.5 mm
Coating	TiAlN
Tool material	Solid carbide
Version	8xD
Point angle	140 °
Shank	DIN 6535 HA to h6
Through-coolant	yes, with 25 bar
Machining strategy	HPC
Semi-Standard	yes
Colour ring	blue
Type of product	Jobber drill

User data

	Suitability	V_c	ISO code
Steel $< 500 \text{ N/mm}^2$	suitable	90 m/min	P
Steel $< 750 \text{ N/mm}^2$	suitable	75 m/min	P
Steel $< 900 \text{ N/mm}^2$	suitable	70 m/min	P
Steel $< 1100 \text{ N/mm}^2$	suitable	55 m/min	P
Steel $< 1400 \text{ N/mm}^2$	suitable	32 m/min	P
INOX $< 900 \text{ N/mm}^2$	suitable	70 m/min	M
INOX $> 900 \text{ N/mm}^2$	suitable	60 m/min	M
wet maximum	suitable		
wet minimum	suitable		

Services

Shank grinding Type HE

129100 HE