

Garant
Double-ended ring spanner, deeply cranked, Width across flats: 19X22mm

Order data

| | |
|--------------|---------------|
| Order number | 615600 19X22 |
| GTIN | 4062406220990 |
| Item class | 61A |

Description
Version:

Drop-forged. With close tolerance jaw widths.

With easy-grip profile shaft. Exceptional tool life and wear resistance. Ring ends with **HT-Drive** profile.

Standard:

DIN 838 / ISO 3318

Material:

Chrome alloy steel; non-flaking chrome-plated, smoothed finish.

Note:

HT-Drive – the particularly close-fitting profile.

Advantage

- **Bolts are gripped on the flanks.**
- **The corners are protected.**
- **Longer bolt life.**
- **Larger contact surfaces between bolt and tool.**
- **Secure grip and higher torque transmission.**

Technical description

| | |
|---|--------|
| Spanner length L | 300 mm |
| Width across flats 1 | 19 mm |
| Width across flats 2 | 22 mm |
| maximum ring \varnothing D ₂ max | 34 mm |
| maximum ring \varnothing D ₁ max | 29 mm |

| | |
|-----------------------|-----------------------|
| Width across flats | metric |
| Ring setting | 75 degrees |
| Manufacturing process | drop forged |
| Material | Chrome vanadium steel |
| Surface | matt chrome-plated |
| Ring end deep cranked | yes |
| open ring | no |
| Type of product | Spanner |