

Garant**Soft top jaw, Type: 160A****Order data**

Order number	363034 160A
GTIN	4062406221430
Item class	310

Description**Application:**

For realising customised contours and for machining sensitive components.

Note:

Dovetail slide available for quick change of jaws. Version S of steel and A of aluminium. Sawn raw material, only machined on underside. Article 363034 80A may be clamped only to max. 12.5 Nm (12.5 Nm = 0.5 t). Article 363034 120A may be clamped only to max. 34 Nm (34 Nm = 1 t). Article 363034 160A may be clamped only to max. 82.5 Nm (82.5 Nm = 2 t).

Technical description

Jaw width b	160 mm
Jaw height h	38 mm
Jaw length l	66 mm
suitable for colour code	Xtric 125
Material	EN AW-7075
Type of product	Vice jaws

