

**Garant**
**Clamping toolholder STGCR 90°, for indexable inserts TC., right-hand,  
Shank / insert size: 12/11 mm**

**Order data**

Order number	260906 12/11
GTIN	4045197805096
Item class	21T

**Technical description**

Head length $L_1$	19 mm
suitable indexable insert	TC.. 1102..
Insert size	11 mm
Shank size	12 mm
ISO code toolholder	STGCR/L 1212F11
Pack of insert screws	269028 18
Overall length L	80 mm
Functional width $L_4$	16 mm
Standard	DIN ISO 5610
Application type	right-hand
Through-coolant	no
Setting angle $\kappa$	90 degrees
Application	External longitudinal turning
Application	External longitudinal turning
Application	External longitudinal turning

Type of product

Boring bar

---

**Accessories**

Set of insert screws Type 18

269028 18

Torque screwdriver with scale, to take interchangeable blades maximum torque 500 cNm

659957 500