



## ER collet chuck Form AD, BT 40 A = 100, for ER collet size: 25



### Order data

Order number	302767 25
GTIN	4062406230050
Item class	32A

### Description

#### Version:

External and internal taper ground.

- **All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm.**
- **High-quality precision clamping nut.**

#### Application:

For clamping tools with parallel shank in collets to **DIN 6499 Form A and B.**

#### Supplied with:

ER clamping nut.

#### Optional extras:

ER collets No. 308881 – 309434, ER chuck keys No. 309680 – 309745 or No. 613300.

Pull studs (PS) No. 308760 – 308802. Pull stud wrenches No. 308820; 308835.

#### Note:

Matching clamping nut No. 309580 or 309610.

Machining strategy: HPC

Clamping range: 1 - 16 mm

Overhang dimension A: 100 mm

External Ø D: 42 mm

Spare ER clamping nut: 25

ER chuck key: 25

### Technical description

Spare ER clamping nut	25
-----------------------	----

External Ø D	42 mm
ER chuck key	25
Overhang dimension A	100 mm
Clamping range	1 - 16 mm
Clamping Ø D <sub>1</sub>	1-16 mm
Adapter	BT 40 A = 100
Arbor standard	ISO 7388-2
Arbor standard	JIS B6339
Shape	AD
Concentricity	≤ 3 µm
Machining strategy	HPC
Type of product	Collet chuck

---

## Accessories

ER chuck key for ER collet chuck 25	309680 25
-------------------------------------	-----------