



Face mill arbor Form A, BT 40 A = 100, Spigot Ø d1: 32mm



Order data

Order number	303027 32
GTIN	4062406231088
Item class	32A

Description

Version:

Taper shank, spigots, and contact surfaces ground on collar.
All shanks fine bead blasted. Balancing quality G6.3 / 18,000 rpm. Form A.

Supplied with:

Lock screw.

Optional extras:

Pull studs (PS) No. 308760 – 308802. Special toggle spanner No. 309840.

Technical description

Suitable toggle spanner No. 309840	32
External Ø D	78 mm
Spigot Ø d ₁	32 mm
Overhang dimension A	100 mm
Spare milling cutter lock screw No. 309860 / 309861	32
Clamping Ø D ₁	27 mm
Adapter	BT 40 A = 100
Standard	DIN 6357
Arbor standard	JIS B6339
Arbor standard	JIS B6339

Shape	ADB
Balance quality G at rotational speed	G 6.3 at 15,000 rpm
Concentricity	$\leq 5 \mu\text{m}$
Machining strategy	HPC
Type of product	Milling head arbor