

Garant**Indexable insert for turning VC.T 160408, for finish machining, Grade: HU7315-1**

Order data

Order number	261374 HU7315-1
GTIN	4062406381479
Item class	21G

Technical description

Tolerance	G
Feed f	0.03 - 0.25 mm/rev.
Corner radius	0.8 mm
Cutting conditions	continuous
Cutting speed v_c main application	50 - 600 m/min
Finishing/roughing assignment	Finishing
Main application	N
Chip breaker	AF
Grade	HU7315-1
ISO code indexable insert	VCGT 160408

Cutting depth a_p	0.05 - 1.5 mm
Coating	uncoated
Tool material	Carbide
Number of changes/inserts	2
Type of product	Indexable insert for turning