

Garant
HiRunER precision ER collet chuck, SK 40 A = 70, for ER collet size: 20

Order data

Order number	300642 20
GTIN	4062406544560
Item class	31A

Description
Version:

External and internal tapers are ground. All shanks are hard turned for smooth running. Including RFID/Balluffchip bore, high-performance clamping nut up to 25000 rpm.

Advantage:

- **3 µm radial run-out with a 2 µm clamping nut, 6 µm radial run-out with a 5 µm clamping nut.**
- **Extremely strong holding force (up to factor 2 better than the standard ER chuck).**
- **Vibration reduction effect due to 2-part clamping nut (size 11M and 16M 1-piece).**

Application:

For clamping tools with plain shank in collets to DIN 6499 - Form A and B.

Supplied with:
Precision clamping nut.
Optional extras:

Pull studs (PS) No. 308600 – 308806, PS wrenches No. 308820 – 308835, ER chuck keys No. 309757, 309758 (for 11M and 16M); Fahrion ER collets No. 308901 – 309434. ER collets No. 308901 – 309432, hook spanner No. 628400 or torque wrench No. 309749 or 628520.

Note:

- **Clamps only nominal Ø up to shank Ø tolerance h 10.**
- **Do not use the clamping nut in combination with a sealing washer.**
- **Use in combination with Fahrion collets.**
- **The blue design ring must be removed for Fahrion HP 2µm ER collets.**

Use the precision collet chuck always in conjunction with the precision clamping nut No. 309617.

Machining strategy: HSC

Clamping range: 1 - 13 mm

Overhang dimension A: 70 mm

External Ø D: 38 mm
Spare ER clamping nut No. 309617: 20

Technical description

Overhang dimension A	70 mm
Spare ER clamping nut No. 309617	20
Clamping range	1 - 13 mm
External Ø D	38 mm
Clamping Ø D ₁	1-13 mm
Adapter	SK 40 A = 70
Arbor standard	ISO 7388-1
Shape	ADB
Balance quality G at rotational speed	G 2.5 at 25,000 rpm
Concentricity	≤ 3 µm
Machining strategy	HPC
Machining strategy	HSC
Balluffchip bore	yes
Type of product	Collet chuck