

**Garant****Indexable insert for turning DCGW 04T001, CBN (5° / 7°), Cutting edge version: G**

## Order data

Order number	265426 G
GTIN	4062406545802
Item class	21H

## Description

**Version:**

Fitted with 2 cutters.

## Technical description

Cutting speed $v_c$ main application	120 - 160 m/min
ISO code indexable insert	DCGW 04T001
Number of changes/inserts	2
Cutting depth $a_p$	0.03 - 0.12 mm
Corner radius	0.1 mm
Finishing/roughing assignment	Finishing
Cutting conditions	continuous
Cutting edge version	G

Tool material	CBN
Feed f	0.04 - 0.12 mm/rev.
Grade	BU7220
Product name attribute	BU7220
Type of product	Indexable insert for turning

### User data

	Suitability	$V_c$	ISO code
Steel < 55 HRC	suitable		
Steel < 60 HRC	suitable		
Steel < 67 HRC	suitable		
continuous	suitable		
irregular	suitable		
interrupted	suitable		
dry	suitable		