

Garant**Abrasive cap (SiC), 80 grit, Abrasive cap Ø, -length, shape: 1626G****Order data**

Order number	553327 1626G
GTIN	4062406271947
Item class	51E

Description**Version:**

Silicon carbide (SiC) ideal for grinding titanium, aluminium and alloys of those metals.

Application:

The seamlessly formed abrasive caps slide on to the rubber body and are securely held in place by centrifugal force when the machine is running. **Abrasive caps can be replaced quickly and easily** (replace in direction of slots).

Note:

Compatible only for use with ground abrasive cap holder No. 553100.

Technical description

Abrasive cap length	26 mm
Abrasive cap Ø	16 mm
recommended speed	12000 min ⁻¹
Shape	G
Grinding media	Silicon carbide (SiC)

Grinding medium code	SiC
Grit	80
Product name attribute	80 grit
Type of product	Abrasive cap

User data

	Suitability	V _c	ISO code
Alu Mg	suitable		
Carbide (HM)	suitable		
Ti	suitable		
CuZn	suitable		
Plastic, GRP	suitable		
dry	suitable		

Accessories

Abrasive cap holder Head Ø, head length, shape 1626G	553100 1626G
--	--------------