

Garant

Master Turn steel boring bar helical flutes A.. SCLCR 95°, for indexable inserts CC., right-hand, Shank Ø / insert size: 20/09mm


Order data

Order number	260030 20/09
GTIN	4062406575779
Item class	21T

Technical description

Clamping height L_2	18 mm
Series	GARANT Master
Shank Ø D_s	20 mm
Minimum pre-drill Ø D_{min}	22 mm
Pack of insert screws	269028 8
Overall length L	200 mm
suitable indexable insert	CC.. 09T3..
ISO code toolholder	A20R SCLCR/L09
Centre offset L_3	11 mm
Head length L_1	36 mm
Insert size	9 mm
Standard	DIN 8024
Application type	right-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar