

Garant
Master Turn steel boring bar helical flutes A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 10/06mm

Order data

Order number	260031 10/06
GTIN	4062406576707
Item class	21T

Technical description

Centre offset L_3	6 mm
Insert size	6 mm
Series	GARANT Master
Head length L_1	20 mm
Overall length L	125 mm
Minimum pre-drill $\varnothing D_{\min}$	12 mm
Clamping height L_2	9 mm
Shank $\varnothing D_s$	10 mm
ISO code toolholder	A10K SCLCR/L06
suitable indexable insert	CC.. 0602..
Pack of insert screws	269028 7
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar