

Garant
Master Turn steel boring bar helical flutes A.. SCLCL 95°, for indexable inserts CC., left-hand, Shank Ø / insert size: 20/09mm

Order data

Order number	260031 20/09
GTIN	4062406576738
Item class	21T

Technical description

Series	GARANT Master
Minimum pre-drill $\varnothing D_{\min}$	22 mm
Insert size	9 mm
Overall length L	200 mm
Centre offset L_3	11 mm
ISO code toolholder	A20R SCLCR/L09
suitable indexable insert	CC.. 09T3..
Shank $\varnothing D_s$	20 mm
Head length L_1	36 mm
Pack of insert screws	269028 8
Clamping height L_2	18 mm
Standard	DIN 8024
Application type	left-hand
Boring depth up to	3×D
Through-coolant	yes
Application	Internal longitudinal turning

Type of product

Boring Bar